


## TORQ CONTROL®, main assets



Ref. 15501 - TORQ CONTROL®  
+ connection for lubricating spray

- **Micro Head for increased visibility and easy access in the mouth.**
- **High precision** : exact control of torque (7 torque values : 10 – 15 – 20 – 25 – 30 – 32 – 35 N.cm).
- **Optimum security** : tightening automatically stops when the selected torque is reached.
- **Universal torque wrench** : recommended with any implant system.
- **Lightweight** for a better freedom of movement : **only 135g !**
- **Ergonomic design** : total control in the hand.
- **Easy maintenance** : TORQ CONTROL® can withstand sterilization in an autoclave at 135°C, and its one-piece design with smooth surface limits bacterial retention.

Main competitors	TORQ CONTROL® advantages
<b>Automatic system</b>	
 <p><b>W&amp;H - Prosthodontic screwdriver</b> 8 → 40 N.cm</p>	<ul style="list-style-type: none"> <li>+ <b>Competitive price.</b></li> <li>+ <b>Ergonomics</b> : one-piece design.</li> <li>+ <b>Lightweight</b> : <b>only 135 g !</b></li> <li>+ <b>Visibility</b> : thanks to the micro push-button head.</li> </ul>
 <p><b>NSK - iSD 900 <i>NEW!</i></b> 10 → 40 N.cm</p> <ul style="list-style-type: none"> <li>- Adjustable speed : 10, 20 and 25 rpm.</li> <li>- Calibration bur.</li> <li>- Torque : from 10 to 40 N.cm.</li> <li>- Reverse rotation.</li> <li>- Battery charging time : 90 min.</li> </ul>	<ul style="list-style-type: none"> <li>+ <b>Ergonomics</b> : one-piece design.</li> <li>+ <b>Lightweight</b> : <b>135 g</b> only vs 148 g (contra-angle + motor).</li> <li>+ <b>Visibility</b> : thanks to the micro push-button head.</li> </ul>
<b>Manual system</b>	
<p><b>EUROTEKNIKA - Dynamometric wrench</b></p>  <p>10 → 75 N.cm</p>	<ul style="list-style-type: none"> <li>+ <b>High precision.</b></li> <li>+ <b>Universal</b> (avoid need for multiple ratchet wrenches).</li> <li>+ <b>Accuracy.</b></li> <li>+ <b>More comfortable for the patient.</b></li> </ul>